

Machine for automatic opening of medication boxes and removal of blisters from these boxes fast and easily. The Deboxmatic® L17 saves money and saves your employees' hands.

Main Features:

- Deboxing of any type of medication blisters
- Box dimensions: minimum LxWxH 70x30x18 mm
maximum LxWxH 160x80x40 mm
- Box dimensions up to: LxWxH 160x80x80 mm, by using a special, optional, tool
- Automatic stacking of blisters into stacks that can be placed in the magazine of a Deblimatic deblistering machine.



Since 'seeing is believing', please look at a short video of the Deboxmatic® L17 by clicking on the following link: [Deboxmatic L17 in action](#)

The blisters are automatically stacked in order to facilitate feeding them to an automatic deblistering machine.

The Deboxmatic® L17 is supplied with one standard box opening tool which is suitable for the opening of boxes with dimensions up to 160x80x40 millimeters. As indicated above the machine can open boxes with dimensions up to 160x80x80 millimeters by installing a special box opening tool. The latter tool should be ordered separately if needed.



One Deboxmatic L17 machine can feed at least one automatic Deblimatic L16 or Deblimatic A19 deblistering machine and depending on the number of blisters per box even two Deblimatics. In the above picture the blisters from the Deboxmatic (on the right) can be fed immediately to the Deblimatic L16 (on the left).

Indicative operational performance data:

Maximum deboxing speed: 15 boxes per minute.

Deboxing percentage: > 95 %

*The above-mentioned deboxing speed and percentage are examples of what has been achieved and depend on the type of box and number of blisters in the box. Hence, they don't constitute any legally binding specification.

One Deboxmatic L17 can open and unpack approx. twice the number of boxes that can be opened/unpacked by a person in the same amount of time. So, the Deboxmatic L17 plus one operator can replace two people, hence, saving the cost of one employee. Therefore, the payback time of a Deblimatic L17 is usually close to one year.

Electrical connection data:

Voltage: 220 – 240 Volt 50Hz

Average power consumption during operation: 0.5 kW

Fuse: 16 Amp automatic

Operating temperature range: 10 – 30 °C

Machine dimensions: 900 x 600 x 1500 mm

Weight: approx. 65 kg



Address : Willem Barentszstraat 7d
7825 VZ Emmen, The Netherlands

Tel. : +31 (0)591 391 064

Mobile : +31 (0)626 672 930

www.langemaat.eu

Bank : Rabobank Emmen

IBAN : NL17 RABO 0318 0837 01

Reg.-number : 75248123

VAT-number : NL8602.07.213.B01

info@langemaatontwikkelingentechniek.nl